

**Garant**
**Left-hand thread blind hole machine tap, uncoated, Type: 1-24**

**Order data**

Order number	130041 1-24
GTIN	4062406046576
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 24

Thread Ø: 25.4 mm

Overall length L: 160 mm

Shank Ø D<sub>s</sub>: 20 mm

Shank square □: 16 mm

Tapping hole Ø: 24.5 mm

**Technical description**

Threads per inch	24
Shank square □	16 mm
Thread pitch	1.058 mm
Standard	DIN 376
Shank Ø D <sub>s</sub>	20 mm
Thread Ø	25.4 mm
Tool material	HSS E

Overall length L	160 mm
Thread depth	63.5 mm
Tapping hole Ø	24.5 mm
Number of cutting edges Z	4
Number of clamping slots	4
Thread type	UNS-LH
Thread size	1-24 UNS LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap