

Garant**Left-hand thread blind hole machine tap, uncoated, Type: 3/8-40****Order data**

Order number	130041 3/8-40
GTIN	4062406045890
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 371

Threads per inch: 40

Thread \varnothing : 9.525 mm

Overall length L: 100 mm

Shank \varnothing D_s: 10 mm

Shank square \square : 8 mm

Tapping hole \varnothing : 9 mm

Technical description

Overall length L	100 mm
Thread pitch	0.635 mm
Threads per inch	40
Standard	DIN 371
Shank \varnothing D _s	10 mm
Number of cutting edges Z	3
Tapping hole \varnothing	9 mm

Number of clamping slots	3
Tool material	HSS E
Shank square □	8 mm
Thread depth	23.83 mm
Thread Ø	9.525 mm
Thread type	UNS-LH
Thread size	3/8-40 UNS LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap