

Garant
Left-hand thread blind hole machine tap, uncoated, Type: 1.7/8-14

Order data

Order number	130041 1.7/8-14
GTIN	4062406047528
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 14

Thread Ø: 47.625 mm

Overall length L: 250 mm

Shank Ø D_s: 36 mm

Shank square □: 29 mm

Tapping hole Ø: 46 mm

Technical description

Thread depth	119 mm
Thread Ø	47.625 mm
Shank square □	29 mm
Number of clamping slots	4
Number of cutting edges Z	4
Thread pitch	1.814 mm
Tool material	HSS E

Overall length L	250 mm
Threads per inch	14
Standard	DIN 376
Tapping hole Ø	46 mm
Shank Ø D _s	36 mm
Thread type	UNS-LH
Thread size	1.7/8-14 UNS LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap