

Garant
Machine tap for through holes and blind holes, uncoated, Type: 4-10

Order data

Order number	130050 4-10
GTIN	4062406053024
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS

Tool material: HSS

Threads per inch: 10

Thread Ø: 101.6 mm

Overall length L: 180 mm

Shank Ø D_s: 56 mm

Shank square □: 44 mm

Tapping hole Ø: 99.3 mm

Technical description

Overall length L	180 mm
Shank square □	44 mm
Thread pitch	2.54 mm
Shank Ø D _s	56 mm
Thread depth	152.4 mm
Threads per inch	10
Number of clamping slots	12
Thread Ø	101.6 mm

Tool material	HSS
Tapping hole Ø	99.3 mm
Number of cutting edges Z	12
Thread type	UNS
Thread size	4-10 UNS
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for blind holes and through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap