

Garant
Left-hand thread blind hole machine tap, uncoated, Type: NO.5-40

Order data

Order number	130041 NO.5-40
GTIN	4062406045531
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 3 pcs.
 Special / custom-made product - return not possible
 Thread type: UNC-LH
 Tool material: HSS E
 Standard: DIN 371
 Threads per inch: 40
 Thread \varnothing : 3.175 mm
 Overall length L: 56 mm
 Shank \varnothing D_s : 3.5 mm
 Shank square \square : 2.7 mm
 Tapping hole \varnothing : 2.59 mm

Technical description

Tool material	HSS E
Tapping hole \varnothing	2.59 mm
Overall length L	56 mm
Shank \varnothing D_s	3.5 mm
Threads per inch	40
Shank square \square	2.7 mm
Standard	DIN 371

Thread depth	7.9 mm
Number of cutting edges Z	3
Number of clamping slots	3
Thread pitch	0.635 mm
Thread Ø	3.175 mm
Thread type	UNC-LH
Thread size	5-40 UNC LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap