

Garant**Left-hand thread blind hole machine tap, uncoated, Type: 9/16-12****Order data**

Order number	130041 9/16-12
GTIN	4062406046200
Item class	10N

Description**Note:**

Delivery time: 35 calendar days
Minimum order quantity: 2 pcs.
Special / custom-made product - return not possible
Thread type: UNC-LH
Tool material: HSS E
Standard: DIN 376
Threads per inch: 12
Thread \varnothing : 14.288 mm
Overall length L: 110 mm
Shank \varnothing D_s: 11 mm
Shank square \square : 9 mm
Tapping hole \varnothing : 12.15 mm

Technical description

Number of clamping slots	3
Number of cutting edges Z	3
Thread \varnothing	14.288 mm
Overall length L	110 mm
Standard	DIN 376
Threads per inch	12
Thread depth	35.72 mm

Tapping hole Ø	12.15 mm
Thread pitch	2.117 mm
Shank Ø D _s	11 mm
Tool material	HSS E
Shank square □	9 mm
Thread type	UNC-LH
Thread size	9/16-12 UNC LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap