

**Garant**
**Left-hand thread blind hole machine tap, uncoated, Type: 2-18**

**Order data**

Order number	130041 2-18
GTIN	4062406047610
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 18

Thread  $\varnothing$ : 50.8 mm

Overall length L: 250 mm

Shank  $\varnothing$  D<sub>s</sub>: 40 mm

Shank square  $\square$ : 32 mm

Tapping hole  $\varnothing$ : 49.5 mm

**Technical description**

Thread depth	127 mm
Tool material	HSS E
Number of clamping slots	4
Shank $\varnothing$ D <sub>s</sub>	40 mm
Standard	DIN 376
Tapping hole $\varnothing$	49.5 mm
Thread pitch	1.411 mm

Overall length L	250 mm
Number of cutting edges Z	4
Threads per inch	18
Shank square □	32 mm
Thread Ø	50.8 mm
Thread type	UNS-LH
Thread size	2-18 UNS LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap