

**Garant****Left-hand thread blind hole machine tap, uncoated, Type: 9/16-14****Order data**

Order number	130041 9/16-14
GTIN	4062406046194
Item class	10N

**Description****Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 14

Thread  $\varnothing$ : 14.288 mm

Overall length L: 110 mm

Shank  $\varnothing$  D<sub>s</sub>: 11 mm

Shank square  $\square$ : 9 mm

Tapping hole  $\varnothing$ : 12.6 mm

**Technical description**

Number of cutting edges Z	3
Tapping hole $\varnothing$	12.6 mm
Number of clamping slots	3
Threads per inch	14
Shank $\varnothing$ D <sub>s</sub>	11 mm
Overall length L	110 mm
Thread pitch	1.814 mm

Tool material	HSS E
Thread depth	35.72 mm
Standard	DIN 376
Thread Ø	14.288 mm
Shank square □	9 mm
Thread type	UNS-LH
Thread size	9/16-14 UNS LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap