

**Garant**
**Blind hole machine tap, TiN, Type: 1.3/8-8**

**Order data**

Order number	130045 1.3/8-8
GTIN	4062406049270
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS E

Standard: DIN 376

Threads per inch: 8

Thread Ø: 34.925 mm

Overall length L: 200 mm

Shank Ø D<sub>s</sub>: 28 mm

Shank square □: 22 mm

Tapping hole Ø: 31.9 mm

**Technical description**

Thread depth	87.31 mm
Threads per inch	8
Thread pitch	3.175 mm
Number of clamping slots	4
Tool material	HSS E
Shank Ø D <sub>s</sub>	28 mm
Thread Ø	34.925 mm

Standard	DIN 376
Number of cutting edges Z	4
Overall length L	200 mm
Tapping hole $\varnothing$	31.9 mm
Shank square $\square$	22 mm
Thread type	UN
Thread size	1.3/8-8 UN
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap