

Garant
Left-hand thread blind hole machine tap, uncoated, Type: NO.10-36

Order data

Order number	130041 NO.10-36
GTIN	4062406045616
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 3 pcs.
 Special / custom-made product - return not possible
 Thread type: UNS-LH
 Tool material: HSS E
 Standard: DIN 371
 Threads per inch: 36
 Thread \varnothing : 4.826 mm
 Overall length L: 70 mm
 Shank \varnothing D_s: 6 mm
 Shank square \square : 4.9 mm
 Tapping hole \varnothing : 4.15 mm

Technical description

Tool material	HSS E
Number of clamping slots	3
Tapping hole \varnothing	4.15 mm
Standard	DIN 371
Overall length L	70 mm
Number of cutting edges Z	3
Threads per inch	36

Thread Ø	4.826 mm
Shank square □	4.9 mm
Thread depth	12.1 mm
Shank Ø D _s	6 mm
Thread pitch	0.706 mm
Thread type	UNS-LH
Thread size	10-36 UNS LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap