

Garant
Left-hand thread through hole and blind hole machine tap, uncoated, Type: 4.3/4-14

Order data

Order number	130051 4.3/4-14
GTIN	4062406054335
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS

Threads per inch: 14

Thread \varnothing : 120.65 mm

Overall length L: 180 mm

Shank \varnothing D_s: 56 mm

Shank square \square : 44 mm

Tapping hole \varnothing : 119 mm

Technical description

Tool material	HSS
Shank \varnothing D _s	56 mm
Thread \varnothing	120.65 mm
Threads per inch	14
Number of cutting edges Z	12
Thread pitch	1.814 mm
Thread depth	180.975 mm

Shank square □	44 mm
Overall length L	180 mm
Tapping hole Ø	119 mm
Number of clamping slots	12
Thread type	UNS-LH
Thread size	4.3/4-14 UNS LH
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for blind holes and through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap