

**Garant**
**Machine tap for through holes and blind holes, TiN, Type: 2.7/8-12**

**Order data**

Order number	130055 2.7/8-12
GTIN	4062406054830
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS

Threads per inch: 12

Thread  $\varnothing$ : 73.025 mm

Overall length L: 160 mm

Shank  $\varnothing D_s$ : 50 mm

Shank square  $\square$ : 39 mm

Tapping hole  $\varnothing$ : 71 mm

**Technical description**

Number of cutting edges Z	8
Thread pitch	2.11 mm
Thread depth	109.54 mm
Thread $\varnothing$	73.025 mm
Shank $\varnothing D_s$	50 mm
Tool material	HSS
Tapping hole $\varnothing$	71 mm
Overall length L	160 mm

Threads per inch	12
Number of clamping slots	8
Shank square □	39 mm
Thread type	UN
Thread size	2.7/8-12 UN
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for blind holes and through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap