

Garant**Machine tap for through holes and blind holes, TiN, Type: 2.3/8-16****Order data**

Order number	130055 2.3/8-16
GTIN	4062406054571
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS

Threads per inch: 16

Thread \varnothing : 60.325 mm

Overall length L: 160 mm

Shank \varnothing D_s: 50 mmShank square \square : 39 mmTapping hole \varnothing : 58.85 mm**Technical description**

Tapping hole \varnothing	58.85 mm
Thread \varnothing	60.325 mm
Tool material	HSS
Threads per inch	16
Shank square \square	39 mm
Number of cutting edges Z	6
Overall length L	160 mm
Number of clamping slots	6

Thread depth	90.49 mm
Shank $\varnothing D_s$	50 mm
Thread pitch	1.588 mm
Thread type	UN
Thread size	2.3/8-16 UN
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5xD for blind holes and through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap