

Garant
Blind hole machine tap, TiN, Type: 1.5/16-20

Order data

Order number	130045 1.5/16-20
GTIN	4062406049164
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS E

Standard: DIN 376

Threads per inch: 20

Thread \varnothing : 33.338 mm

Overall length L: 200 mm

Shank $\varnothing D_s$: 28 mm

Shank square \square : 22 mm

Tapping hole \varnothing : 32.15 mm

Technical description

Tapping hole \varnothing	32.15 mm
Shank square \square	22 mm
Shank $\varnothing D_s$	28 mm
Tool material	HSS E
Standard	DIN 376
Thread \varnothing	33.338 mm
Thread pitch	1.27 mm

Threads per inch	20
Number of cutting edges Z	4
Overall length L	200 mm
Thread depth	83.3 mm
Number of clamping slots	4
Thread type	UN
Thread size	1.5/16-20 UN
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap