

Garant**Left-hand thread blind hole machine tap, uncoated, Type: 9/16-20****Order data**

Order number	130041 9/16-20
GTIN	4062406046163
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 20

Thread Ø: 14.288 mm

Overall length L: 110 mm

Shank Ø D_s: 11 mm

Shank square □: 9 mm

Tapping hole Ø: 13.1 mm

Technical description

Thread pitch	1.27 mm
Number of cutting edges Z	3
Threads per inch	20
Standard	DIN 376
Thread Ø	14.288 mm
Thread depth	35.72 mm
Overall length L	110 mm

Tool material	HSS E
Number of clamping slots	3
Tapping hole \varnothing	13.1 mm
Shank $\varnothing D_s$	11 mm
Shank square \square	9 mm
Thread type	UN-LH
Thread size	9/16-20 UN LH
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap