

Garant
Left-hand thread through hole and blind hole machine tap, TiN, Type: 4.1/8-16

Order data

Order number	130056 4.1/8-16
GTIN	4062406056445
Item class	10N

Description
Note:

Delivery time: 49 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: UN-LH
 Tool material: HSS
 Threads per inch: 16
 Thread \varnothing : 104.8 mm
 Overall length L: 180 mm
 Shank $\varnothing D_s$: 56 mm
 Shank square \square : 44 mm
 Tapping hole \varnothing : 103.3 mm

Technical description

Tapping hole \varnothing	103.3 mm
Thread \varnothing	104.8 mm
Threads per inch	16
Shank $\varnothing D_s$	56 mm
Number of cutting edges Z	12
Thread pitch	1.588 mm
Overall length L	180 mm

Tool material	HSS
Number of clamping slots	12
Shank square □	44 mm
Thread depth	157.16 mm
Thread type	UN-LH
Thread size	4.1/8-16 UN LH
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for blind holes and through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap