

Garant**Left-hand thread through hole and blind hole machine tap, TiN, Type: 2.3/4-8****Order data**

Order number	130056 2.3/4-8
GTIN	4062406055929
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS

Threads per inch: 8

Thread \varnothing : 69.85 mm

Overall length L: 160 mm

Shank \varnothing D_s: 50 mmShank square \square : 39 mmTapping hole \varnothing : 66.8 mm**Technical description**

Number of clamping slots	8
Tool material	HSS
Shank \varnothing D _s	50 mm
Shank square \square	39 mm
Tapping hole \varnothing	66.8 mm
Thread pitch	3.175 mm
Threads per inch	8
Overall length L	160 mm

Thread Ø	69.85 mm
Thread depth	104.78 mm
Number of cutting edges Z	8
Thread type	UN-LH
Thread size	2.3/4-8 UN LH
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for blind holes and through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap