

Garant
Blind hole machine tap, TiN, Type: 1.15/16-20

Order data

Order number	130045 1.15/16-20
GTIN	4062406049805
Item class	10N

Description
Note:

Delivery time: 49 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: UN
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 20
 Thread \varnothing : 49.212 mm
 Overall length L: 250 mm
 Shank \varnothing D_s: 40 mm
 Shank square \square : 32 mm
 Tapping hole \varnothing : 48 mm

Technical description

Overall length L	250 mm
Tool material	HSS E
Tapping hole \varnothing	48 mm
Thread depth	123 mm
Number of clamping slots	4
Thread \varnothing	49.212 mm
Number of cutting edges Z	4

Threads per inch	20
Thread pitch	1.27 mm
Shank square □	32 mm
Shank Ø D _s	40 mm
Standard	DIN 376
Thread type	UN
Thread size	1.15/16-20 UN
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap