

Garant
Left-hand thread blind hole machine tap, uncoated, Type: 7/16-24

Order data

Order number	130041 7/16-24
GTIN	4062406046002
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UNS-LH
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 24
 Thread \varnothing : 11.112 mm
 Overall length L: 110 mm
 Shank \varnothing D_s : 9 mm
 Shank square \square : 7 mm
 Tapping hole \varnothing : 10.1 mm

Technical description

Thread pitch	1.058 mm
Number of clamping slots	3
Standard	DIN 376
Thread depth	27.78 mm
Shank \varnothing D_s	9 mm
Thread \varnothing	11.112 mm
Number of cutting edges Z	3

Shank square □	7 mm
Overall length L	110 mm
Tapping hole Ø	10.1 mm
Tool material	HSS E
Threads per inch	24
Thread type	UNS-LH
Thread size	7/16-24 UNS LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap