

Garant
Blind hole machine tap, TiN, Type: 11/16-20

Order data

| | |
|--------------|-----------------|
| Order number | 130045 11/16-20 |
| GTIN | 4062406048549 |
| Item class | 10N |

Description
Note:

Delivery time: 49 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UN
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 20
 Thread \varnothing : 17.462 mm
 Overall length L: 125 mm
 Shank \varnothing D_s: 14 mm
 Shank square \square : 11 mm
 Tapping hole \varnothing : 16.25 mm

Technical description

| | |
|--------------------------|-----------|
| Tool material | HSS E |
| Standard | DIN 376 |
| Thread \varnothing | 17.462 mm |
| Threads per inch | 20 |
| Number of clamping slots | 4 |
| Overall length L | 125 mm |
| Shank square \square | 11 mm |

| | |
|----------------------------------|--|
| Shank $\varnothing D_s$ | 14 mm |
| Thread depth | 43.7 mm |
| Number of cutting edges Z | 4 |
| Thread pitch | 1.27 mm |
| Tapping hole \varnothing | 16.25 mm |
| Thread type | UN |
| Thread size | 11/16-20 UN |
| Coating | TiN |
| Flank angle | 60 ° |
| Thread standard | ASME B1.1 |
| Tolerance class | 1B |
| Tolerance class | 2B +0.20 |
| Tolerance class | 2B +0.10 |
| Tolerance class | 3B |
| Tolerance class | 2B |
| Tolerance class | 2B +0.05 |
| Taper lead form | C |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 2xD for blind holes |
| Cutting direction | right-hand |
| Type of threading tool | Machine tap for conventional machining |
| Colour ring | without |
| Type of product | Tap |