

Garant
Blind hole machine tap, TiN, Type: 13/16-12

Order data

Order number	130045 13/16-12
GTIN	4062406048679
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS E

Standard: DIN 376

Threads per inch: 12

Thread Ø: 20.638 mm

Overall length L: 140 mm

Shank Ø D_s: 18 mm

Shank square □: 14.5 mm

Tapping hole Ø: 18.6 mm

Technical description

Overall length L	140 mm
Shank Ø D _s	18 mm
Thread pitch	2.117 mm
Tool material	HSS E
Threads per inch	12
Standard	DIN 376
Number of cutting edges Z	4

Thread depth	51.6 mm
Tapping hole Ø	18.6 mm
Number of clamping slots	4
Thread Ø	20.638 mm
Shank square □	14.5 mm
Thread type	UN
Thread size	13/16-12 UN
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap