

**Garant**
**Blind hole machine tap, TiN, Type: 9/16-14**

**Order data**

Order number	130045 9/16-14
GTIN	4062406048433
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days  
 Minimum order quantity: 2 pcs.  
 Special / custom-made product - return not possible  
 Thread type: UNS  
 Tool material: HSS E  
 Standard: DIN 376  
 Threads per inch: 14  
 Thread  $\varnothing$ : 14.288 mm  
 Overall length L: 110 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 11 mm  
 Shank square  $\square$ : 9 mm  
 Tapping hole  $\varnothing$ : 12.6 mm

**Technical description**

Standard	DIN 376
Shank square $\square$	9 mm
Number of cutting edges Z	3
Tool material	HSS E
Thread depth	35.72 mm
Overall length L	110 mm
Tapping hole $\varnothing$	12.6 mm

Number of clamping slots	3
Thread pitch	1.814 mm
Thread Ø	14.288 mm
Shank Ø D <sub>s</sub>	11 mm
Threads per inch	14
Thread type	UNS
Thread size	9/16-14 UNS
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap