

Garant
Left-hand thread blind hole machine tap, TiN, Type: 1.1/2-10

Order data

Order number	130046 1.1/2-10
GTIN	4062406051648
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 10

Thread Ø: 38.1 mm

Overall length L: 200 mm

Shank Ø D_s: 32 mm

Shank square □: 24 mm

Tapping hole Ø: 35.7 mm

Technical description

Overall length L	200 mm
Thread Ø	38.1 mm
Number of cutting edges Z	4
Threads per inch	10
Thread depth	95.25 mm
Number of clamping slots	4
Standard	DIN 376

Tapping hole Ø	35.7 mm
Thread pitch	2.54 mm
Shank Ø D _s	32 mm
Tool material	HSS E
Shank square □	24 mm
Thread type	UNS-LH
Thread size	1.1/2-10 UNS LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap