

Garant
Blind hole machine tap, TiN, Type: 5/8-24

Order data

Order number	130045 5/8-24
GTIN	4062406048464
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNEF

Tool material: HSS E

Standard: DIN 376

Threads per inch: 24

Thread Ø: 15.875 mm

Overall length L: 110 mm

Shank Ø D_s: 12 mm

Shank square □: 9 mm

Tapping hole Ø: 15 mm

Technical description

Number of cutting edges Z	3
Overall length L	110 mm
Thread Ø	15.875 mm
Tool material	HSS E
Shank square □	9 mm
Thread pitch	1.058 mm
Threads per inch	24

Thread depth	39.7 mm
Number of clamping slots	3
Shank $\varnothing D_s$	12 mm
Tapping hole \varnothing	15 mm
Standard	DIN 376
Thread type	UNEF
Thread size	5/8-24 UNEF
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap