

Garant
Left-hand thread blind hole machine tap, TiN, Type: 1.1/4-10

Order data

Order number	130046 1.1/4-10
GTIN	4062406051372
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 10

Thread \varnothing : 31.75 mm

Overall length L: 180 mm

Shank \varnothing D_s: 25 mm

Shank square \square : 20 mm

Tapping hole \varnothing : 29.5 mm

Technical description

Number of clamping slots	4
Tapping hole \varnothing	29.5 mm
Number of cutting edges Z	4
Shank square \square	20 mm
Threads per inch	10
Shank \varnothing D _s	25 mm
Standard	DIN 376

Tool material	HSS E
Thread Ø	31.75 mm
Thread depth	79.38 mm
Overall length L	180 mm
Thread pitch	2.54 mm
Thread type	UNS-LH
Thread size	1.1/4-10 UNS LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap