

Garant
Left-hand thread blind hole machine tap, TiN, Type: 1.15/16-12

Order data

Order number	130046 1.15/16-12
GTIN	4062406052065
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 12

Thread \varnothing : 49.212 mm

Overall length L: 250 mm

Shank \varnothing D_s: 40 mm

Shank square □: 32 mm

Tapping hole \varnothing : 47.2 mm

Technical description

Number of cutting edges Z	4
Overall length L	250 mm
Threads per inch	12
Number of clamping slots	4
Thread pitch	2.117 mm
Shank \varnothing D _s	40 mm
Tapping hole \varnothing	47.2 mm

Thread Ø	49.212 mm
Shank square □	32 mm
Tool material	HSS E
Standard	DIN 376
Thread depth	123 mm
Thread type	UN-LH
Thread size	1.15/16-12 UN LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap