

Garant**GPCT S50102, Grade: HU7310****Order data**

Order number	268560 HU7310
GTIN	4062406057510
Item class	211

Technical description

Corner radius	0.2 mm
Cutting speed v_c main application	50 - 300 m/min
Cutting conditions	continuous
Cutting depth a_p	0.05 - 1.6 mm
Finishing/roughing assignment	Finishing
Feed f	0.03 - 0.25 mm/rev.
Grade	HU7310
Tool material	Carbide
Main application	N
Chip breaker	AF
Coating	uncoated

ISO code indexable insert	GPCT S50102
Number of changes/inserts	2
Type of product	Indexable insert for turning