

**Garant**

**Shrink fit chuck extension 3°, vibration-damped, L = 300 mm, Ø d / Ø D1:  
25/16 mm**


**Order data**

Order number	302417 25/16
GTIN	4045197701930
Item class	31P

**Description**
**Version:**

Shank bored through for internal coolant supply (ICS) up to maximum 80 bar. Including length adjustment backstop screw. A **carbide core embedded** in the adapter damps the tendency to vibrate.

Maximum permissible speed 8,000 rpm.

**Advantage:**

- **Avoid vibrations in the clamping system.**
- **Better workpiece surface finishes.**
- **Increased tool service lives.**

Vibration: damped

Ø D<sub>2</sub>: 22 mm

**Technical description**

Ø D <sub>2</sub>	22 mm
Bore Ø D <sub>1</sub>	16 mm
Shank Ø d	25 mm
Overall length L	300 mm
Product name attribute	L = 300 mm
Through-coolant	yes, with max. 80 bar
Vibration	damped
Type of product	Shrink fit chuck accessories

