



Digital external micrometer, Measuring range: 50-75mm



Order data

Order number	421490 50-75
GTIN	4045197701893
Item class	42B

Description

Version:

Easy-to-read display. Carbide-tipped anvils.

Digital and analogue graduations. Dust-proof and splash-proof metal casing.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

1 battery No. 081560 size 357. 1 plug-in sphere for measuring curved surfaces.

From size 25–50, 1 micrometer standard.

Technical description

Spindle pitch	0.5 mm
Spindle Ø	6.5 mm
Measuring range	50 - 75 mm
Error limit	5 µm
Scale divisions	0.001 mm
Calibration	B1
Calibration	B2
#Number of batteries contained	1
#Article no of the battery / rechargeable battery fitted	081560 357

IP Index of Protection	IP 54
Power supply	Battery-powered
Standard	DIN 863
Measurement technology	digital
Packaging	sturdy box
Type of product	External tube micrometer

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/421490-50-75>