

Garant
Left-hand thread blind hole machine tap, TiN, Type: 3/8-20

Order data

Order number	130046 3/8-20
GTIN	4062406050429
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 371

Threads per inch: 20

Thread \varnothing : 9.525 mm

Overall length L: 100 mm

Shank \varnothing D_s: 10 mm

Shank square \square : 8 mm

Tapping hole \varnothing : 8.3 mm

Technical description

Number of cutting edges Z	3
Shank square \square	8 mm
Shank \varnothing D _s	10 mm
Overall length L	100 mm
Thread \varnothing	9.525 mm
Threads per inch	20
Tapping hole \varnothing	8.3 mm

Number of clamping slots	3
Thread pitch	1.27 mm
Standard	DIN 371
Tool material	HSS E
Thread depth	23.83 mm
Thread type	UN-LH
Thread size	3/8-20 UN LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap