

Garant
Left-hand thread blind hole machine tap, TiN, Type: 1.15/16-20

Order data

Order number	130046 1.15/16-20
GTIN	4062406052041
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 20

Thread \varnothing : 49.212 mm

Overall length L: 250 mm

Shank \varnothing D_s: 40 mm

Shank square \square : 32 mm

Tapping hole \varnothing : 48 mm

Technical description

Threads per inch	20
Number of cutting edges Z	4
Shank \varnothing D _s	40 mm
Overall length L	250 mm
Tool material	HSS E
Tapping hole \varnothing	48 mm
Shank square \square	32 mm

Thread pitch	1.27 mm
Standard	DIN 376
Number of clamping slots	4
Thread depth	123 mm
Thread Ø	49.212 mm
Thread type	UN-LH
Thread size	1.15/16-20 UN LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap