

Garant**Left-hand thread blind hole machine tap, TiN, Type: 1.1/8-12****Order data**

Order number	130046 1.1/8-12
GTIN	4062406051235
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNF-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 12

Thread Ø: 28.575 mm

Overall length L: 180 mm

Shank Ø D_s: 22 mm

Shank square □: 18 mm

Tapping hole Ø: 26.5 mm

Technical description

Number of clamping slots	4
Overall length L	180 mm
Shank square □	18 mm
Thread Ø	28.575 mm
Tool material	HSS E
Thread depth	71.44 mm
Standard	DIN 376

Threads per inch	12
Thread pitch	2.117 mm
Number of cutting edges Z	4
Shank $\varnothing D_s$	22 mm
Tapping hole \varnothing	26.5 mm
Thread type	UNF-LH
Thread size	1.1/8-12 UNF LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap