


Garant**SNMG 120412, Grade: HB7210-1****Order data**

Order number	251226 HB7210-1
GTIN	4062406059064
Item class	21G

Description

SNMG 120412 HB7210-1 Corner radius: 1.2 mm
Grade: HB7210-1
Chip breaker: GM
Cutting depth a_p : 0.4 - 6.5 mm
Feed f : 0.3 - 0.7 mm/rev.
Cutting speed v_c main application: 100 - 450 m/min

Technical description

Cutting speed v_c main application	100 - 450 m/min
Tool material	Carbide
Feed f	0.3 - 0.7 mm/rev.
Corner radius	1.2 mm
Cutting conditions	slightly interrupted
Chip breaker	GM

Finishing/roughing assignment	Semi-roughing
Cutting depth a_p	0.4 - 6.5 mm
Grade	HB7210-1
Main application	K
Coating	TiCN
ISO code indexable insert	SNMG 120412
Number of changes/inserts	8
Type of product	Indexable insert for turning