

**Garant****Left-hand thread blind hole machine tap, TiN, Type: 1/2-28****Order data**

Order number	130046 1/2-28
GTIN	4062406050535
Item class	10N

**Description****Note:**

Delivery time: 49 calendar days  
Minimum order quantity: 2 pcs.  
Special / custom-made product - return not possible  
Thread type: UNEF-LH  
Tool material: HSS E  
Standard: DIN 376  
Threads per inch: 28  
Thread Ø: 12.7 mm  
Overall length L: 110 mm  
Shank Ø D<sub>s</sub>: 11 mm  
Shank square □: 9 mm  
Tapping hole Ø: 11.8 mm

**Technical description**

Threads per inch	28
Overall length L	110 mm
Standard	DIN 376
Thread depth	31.75 mm
Thread pitch	0.907 mm
Thread Ø	12.7 mm
Tapping hole Ø	11.8 mm

Shank $\varnothing D_s$	11 mm
Shank square $\square$	9 mm
Number of cutting edges Z	3
Number of clamping slots	3
Tool material	HSS E
Thread type	UNEF-LH
Thread size	1/2-28 UNEF LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap