


CNMG 120408, Grade: CA025P

Order data

Order number	250104 CA025P
GTIN	4960664857197
Item class	25E

Description

CNMG 120408 CA025P Grade: CA025P
 Chip breaker: PQ
 Cutting depth a_p : 0.2 - 2.5 mm
 Feed f : 0.13 - 0.4 mm/rev.
 Cutting speed v_c main application: 105 - 435 m/min

Technical description

Feed f	0.13 - 0.4 mm/rev.
Cutting speed v_c main application	105 - 435 m/min
Cutting depth a_p	0.2 - 2.5 mm
Main application	P
Grade	CA025P
Cutting conditions	slightly interrupted
Chip breaker	PQ

Finishing/roughing assignment	Finishing
Tool material	Carbide
Corner radius	0.8 mm
Coating	CVD
ISO code indexable insert	CNMG 120408
Number of changes/inserts	4
Type of product	Indexable insert for turning