


SNMG 120408, Grade: CA025P

Order data

Order number	251356 CA025P
GTIN	4960664864782
Item class	25E

Technical description

Main application	P
Corner radius	0.8 mm
Finishing/roughing assignment	Roughing
Grade	CA025P
Tool material	Carbide
Chip breaker	PH
Cutting conditions	slightly interrupted
Feed f	0.25 - 0.8 mm/rev.
Cutting speed v_c main application	70 - 420 m/min
Cutting depth a_p	1 - 10 mm
Coating	CVD
ISO code indexable insert	SNMG 120408

Number of changes/inserts	8
Type of product	Indexable insert for turning