


WNMG 080408, Grade: CA025P

Order data

Order number	252014 CA025P
GTIN	4960664865819
Item class	25E

Description

WNMG 080408 CA025P Grade: CA025P

Chip breaker: HQ

Cutting depth a_p : 0.5 - 2 mm

Feed f : 0.07 - 0.3 mm/rev.

Cutting speed v_c main application: 70 - 420 m/min

Technical description

Cutting conditions	slightly interrupted
Tool material	Carbide
Grade	CA025P
Corner radius	0.8 mm
Finishing/roughing assignment	Finishing
Chip breaker	HQ
Cutting speed v_c main application	70 - 420 m/min
Feed f	0.07 - 0.3 mm/rev.

Cutting depth a_p	0.5 - 2 mm
Main application	P
Coating	CVD
ISO code indexable insert	WNMG 080408
Number of changes/inserts	6
Type of product	Indexable insert for turning