

**Garant****Left-hand thread blind hole machine tap, TiN, Type: 11/16-24****Order data**

Order number	130046 11/16-24
GTIN	4062406050771
Item class	10N

**Description****Note:**

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNEF-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 24

Thread  $\varnothing$ : 17.462 mm

Overall length L: 125 mm

Shank  $\varnothing$  D<sub>s</sub>: 14 mm

Shank square □: 11 mm

Tapping hole  $\varnothing$ : 16.6 mm**Technical description**

Shank $\varnothing$ D <sub>s</sub>	14 mm
Overall length L	125 mm
Tool material	HSS E
Tapping hole $\varnothing$	16.6 mm
Standard	DIN 376
Thread $\varnothing$	17.462 mm
Threads per inch	24

Shank square □	11 mm
Thread pitch	1.058 mm
Number of clamping slots	4
Thread depth	43.7 mm
Number of cutting edges Z	4
Thread type	UNEF-LH
Thread size	11/16-24 UNF LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap