

Garant
Left-hand thread blind hole machine tap, TiN, Type: 3/8-36

Order data

| | |
|--------------|---------------|
| Order number | 130046 3/8-36 |
| GTIN | 4062406050382 |
| Item class | 10N |

Description
Note:

Delivery time: 49 calendar days
 Minimum order quantity: 3 pcs.
 Special / custom-made product - return not possible
 Thread type: UNS-LH
 Tool material: HSS E
 Standard: DIN 371
 Threads per inch: 36
 Thread \varnothing : 9.525 mm
 Overall length L: 100 mm
 Shank \varnothing D_s: 10 mm
 Shank square \square : 8 mm
 Tapping hole \varnothing : 8.9 mm

Technical description

| | |
|---------------------------|----------|
| Shank square \square | 8 mm |
| Threads per inch | 36 |
| Thread depth | 23.83 mm |
| Thread pitch | 0.706 mm |
| Number of cutting edges Z | 3 |
| Standard | DIN 371 |
| Thread \varnothing | 9.525 mm |

| | |
|----------------------------------|--|
| Overall length L | 100 mm |
| Shank $\varnothing D_s$ | 10 mm |
| Tool material | HSS E |
| Number of clamping slots | 3 |
| Tapping hole \varnothing | 8.9 mm |
| Thread type | UNS-LH |
| Thread size | 3/8-36 UNS LH |
| Coating | TiN |
| Thread standard | ASME B1.1 |
| Tolerance class | 1B |
| Tolerance class | 2B +0.20 |
| Tolerance class | 2B +0.10 |
| Tolerance class | 3B |
| Tolerance class | 2B |
| Tolerance class | 2B +0.05 |
| Taper lead form | C |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 2×D for blind holes |
| Cutting direction | left-hand |
| Type of threading tool | Machine tap for conventional machining |
| Colour ring | without |
| Type of product | Tap |