

**Garant****Left-hand thread blind hole machine tap, TiN, Type: 9/16-14****Order data**

Order number	130046 9/16-14
GTIN	4062406050672
Item class	10N

**Description****Note:**

Delivery time: 49 calendar days  
Minimum order quantity: 2 pcs.  
Special / custom-made product - return not possible  
Thread type: UNS-LH  
Tool material: HSS E  
Standard: DIN 376  
Threads per inch: 14  
Thread  $\varnothing$ : 14.288 mm  
Overall length L: 110 mm  
Shank  $\varnothing$  D<sub>s</sub>: 11 mm  
Shank square  $\square$ : 9 mm  
Tapping hole  $\varnothing$ : 12.6 mm

**Technical description**

Overall length L	110 mm
Shank square $\square$	9 mm
Thread depth	35.72 mm
Tapping hole $\varnothing$	12.6 mm
Thread $\varnothing$	14.288 mm
Standard	DIN 376
Number of clamping slots	3

Threads per inch	14
Number of cutting edges Z	3
Tool material	HSS E
Shank $\varnothing D_s$	11 mm
Thread pitch	1.814 mm
Thread type	UNS-LH
Thread size	9/16-14 UNS LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap