

Garant**Left-hand thread blind hole machine tap, TiN, Type: NO.10-32****Order data**

Order number	130046 NO.10-32
GTIN	4062406050108
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Thread type: UNF-LH

Tool material: HSS E

Standard: DIN 371

Threads per inch: 32

Thread \varnothing : 4.826 mm

Overall length L: 70 mm

Shank \varnothing D_s: 6 mmShank square \square : 4.9 mmTapping hole \varnothing : 4.1 mm**Technical description**

Threads per inch	32
Shank \varnothing D _s	6 mm
Number of cutting edges Z	3
Number of clamping slots	3
Thread \varnothing	4.826 mm
Tapping hole \varnothing	4.1 mm
Standard	DIN 371

Overall length L	70 mm
Shank square □	4.9 mm
Thread depth	12.1 mm
Tool material	HSS E
Thread pitch	0.794 mm
Thread type	UNF-LH
Thread size	10-32 UNF LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap