

Garant**Left-hand thread blind hole machine tap, TiN, Type: 9/16-18****Order data**

Order number	130046 9/16-18
GTIN	4062406050658
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNF-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 18

Thread \varnothing : 14.288 mm

Overall length L: 110 mm

Shank \varnothing D_s: 11 mmShank square \square : 9 mmTapping hole \varnothing : 12.9 mm**Technical description**

Thread depth	35.72 mm
Standard	DIN 376
Tool material	HSS E
Number of cutting edges Z	3
Number of clamping slots	3
Overall length L	110 mm
Shank \varnothing D _s	11 mm

Tapping hole Ø	12.9 mm
Threads per inch	18
Thread Ø	14.288 mm
Shank square □	9 mm
Thread pitch	1.411 mm
Thread type	UNF-LH
Thread size	9/16-18 UNF LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap