



Bridge reamer, uncoated, Nominal \varnothing DC k11: 6,4mm



Order data

Order number	162800 6,4
GTIN	4062406064358
Item class	120

Description

Version:

Tapering flute form with a length of approx. $3 \times$ nominal \varnothing . Very sturdy due to strong core and radius heel of flutes. Easy, peeling cut by spiral flutes; number of flutes varies according to the size.

Application:

Particularly useful for the installation of components; for reaming offset holes or enlarging rivet holes. Bridge reamers are used on pneumatic hand-held drills in boiler construction.

Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Technical description

Overhang L_1	85.5 mm
Flute length L_c	75 mm
Morse taper MT size	1
Feed f in steel $< 500 \text{ N/mm}^2$	0.12 mm/rev.
Overall length L	151 mm
Number of cutting edges Z	3
Minor \varnothing	4.5 mm
Nominal $\varnothing D_c$	6.4 mm
Tolerance nominal \varnothing	k11
Coating	uncoated

Tool material	HSS
Standard	DIN 311
Helix angle	25 degrees
Through-coolant	no
Shank	Morse taper
Application for type of drilling	for through holes
Colour ring	without
Type of product	Phillips bit

User data

	Suitability	V _c	ISO code
Aluminium	suitable	20 m/min	N
Aluminium (short chipping)	suitable	20 m/min	N
Steel < 500 N/mm ²	suitable	15 m/min	P
Steel < 750 N/mm ²	suitable	10 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	7 m/min	P
Oil	suitable		
wet maximum	suitable		