

Garant

**Indexable face mill 45° right-hand cutting, with bore, Ø D / number of teeth Z:
32/3mm**


Order data

Order number	214200 32/3
GTIN	4045197702319
Item class	210

Description
Note:

Use GARANT torque screwdriver TQ No. **211750 size 5.7** with bit shank No. **674252 size 20IP**.

Technical description

Cutting edge Ø D _c	32 mm
suitable indexable insert	SE.. 1204..
Mounting bore Ø	16 mm
Overall length L _{tot}	40 mm
Pack of insert screws	219800 (20IP; 5.7 Nm)
maximum external Ø D _{max}	44 mm
Number of cutting edges Z	3
Shank type	with bore
Setting angle κ	45 degrees

Spacing of the cutters	unequal spacing
Through-coolant	yes
Machining strategy	MTC
Tool exchange	PowerCard
Type of product	Face mill

Accessories

Set of insert screws 10 pieces	219800
Torque screwdriver, fixed setting set torque 5,7 N·m	211750 5,7
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 20IP	674252 20IP