

Garant**Left-hand thread blind hole machine tap, TiN, Type: NO.2-56****Order data**

Order number	130046 NO.2-56
GTIN	4062406049959
Item class	10N

Description**Note:**

Delivery time: 91 calendar days
Minimum order quantity: 25 pcs.
Special / custom-made product - return not possible
Thread type: UNC-LH
Tool material: HSS E
Standard: DIN 371
Threads per inch: 56
Thread \varnothing : 2.184 mm
Overall length L: 45 mm
Shank \varnothing D_s: 2.8 mm
Shank square \square : 2.1 mm
Tapping hole \varnothing : 1.78 mm

Technical description

Tapping hole \varnothing	1.78 mm
Tool material	HSS E
Thread depth	5.46 mm
Number of clamping slots	3
Standard	DIN 371
Threads per inch	56
Number of cutting edges Z	3

Shank $\varnothing D_s$	2.8 mm
Thread pitch	0.454 mm
Overall length L	45 mm
Thread \varnothing	2.184 mm
Shank square \square	2.1 mm
Thread type	UNC-LH
Thread size	2-56 UNC LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap