

Garant
Boring bar carbide, right-hand, Shank \varnothing / insert size: 25/11 mm

Order data

Order number	260318 25/11
GTIN	4062406065966
Item class	21T

Technical description

Insert size	11 mm
Minimum pre-drill $\varnothing D_{\min}$	32 mm
suitable indexable insert	DC.. 11T3..
Pack of insert screws	269028 8
Overhang L_1	200 mm
Setting angle κ	93 degrees
Centre offset L_3	16 mm
ISO code toolholder	E25S SDUCR/L11
Clamping height L_2	24 mm
Overall length L	250 mm
Shank $\varnothing D_s$	25 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500