

Garant
GARANT Master Steel FEED solid carbide stepped drill, TiAlN, for threads: M5

Order data

Order number	125035 M5
GTIN	4062406066444
Item class	11E

Description
Version:

For generation of **optimum tapping holes**. Creates **ideal machining conditions** for the subsequent tapping tool. The cutter \varnothing of the drill is matched to the thread that is to be produced, in order to achieve a threads true to gauge and for **high process reliability of the tapping process**. The 90° counterbore for the thread is produced **in the same operation** as drilling the tapping hole.

3-flute drill, specially developed for **use at very high feed rates**. Outstandingly suitable for machines with high installed power and stable machining conditions.

Diameter tolerance first level: h7.

Thread type: M

No. of teeth Z: 3

Through-coolant: yes, with 25 bar

Thread pitch: 0.8

$\varnothing D_1$ 1st step: 4.25 mm

$\varnothing D_2$ 2nd step with chamfer h7: 5.5 mm

Step height L_1 1st step: 13.6 mm

Flute length L_c : 28 mm

Overall length L: 66 mm

Technical description

Feed f in steel < 1100 N/mm ²	0.28 mm/rev.
$\varnothing D_2$ 2nd step with chamfer h7	5.5 mm
Flute length L_c	28 mm
Overall length L	66 mm

Shank $\varnothing D_s$	6 mm
for threads	M5
No. of teeth Z	3
Thread pitch	0.8
Thread type	M
Through-coolant	yes, with 25 bar
$\varnothing D_1$ 1st step	4.25 mm
Step height L_1 1st step	13.6 mm
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Tolerance nominal \varnothing	m7
Point angle	145 °
Shank	DIN 6535 HA to h6
Countersink angle	90 °
Machining strategy	HPC
Colour ring	green
Application for type of drilling	for blind hole and through hole
Type of product	Stepped drill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	160 m/min	P
Steel < 750 N/mm ²	suitable	140 m/min	P
Steel < 900 N/mm ²	suitable	130 m/min	P
Steel < 1100 N/mm ²	suitable	110 m/min	P
Steel < 1400 N/mm ²	suitable	90 m/min	P
Steel < 55 HRC	suitable	60 m/min	H

INOX < 900 N/mm ²	suitable	60 m/min	M
INOX > 900 N/mm ²	suitable	50 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	40 m/min	S
GG	suitable	130 m/min	K
GGG	suitable	80 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		