

Garant GRIDLINE

**Top-mounted cabinet with drawer, Viewing window swing doors, 16×16G,
Height: 1000mm****Order data**

Order number	940033 1000
GTIN	4062406067328
Item class	9GI

Description**Version:**

Equipped cabinet in 20×20G, with drawers 16×16G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door. Drawers with front height 125 mm.

Supplied with:

Cabinet with shelves and drawers.

Colour:

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated.**

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Electronic locking system can be retrofitted	yes
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Drawer runner extension (partial/full extension)	100 %
Height	1000 mm
Weight	46 kg
Cabinet fronts	Viewing window swing door
Number of shelves	2
Usable height	845 mm
Drawer/pull-out shelf load capacity	75 kg
Depth	500 mm
Width	500 mm
Number of drawers	1
Handle positioning	bottom
ComfortClose	no
Depth in G	20
Drawer usable depth in G	16
Drawer usable width in G	16
Drawer usable depth	400 mm
Drawer usable width	400 mm
Width in G	20
Drawer usable area in G	16×16
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer usable width × usable depth in G	16×16G
Type of cabinet	Add-on cabinet
Type of product	Cabinet with shelves

Accessories

Drawer for swing-door cabinets,Width 20G Drawer front height 150 mm	940640 150
Slide handle for GridLine Type GP11	914226 GP11
Drawer for swing-door cabinets,Width 20G Drawer front height 75 mm	940640 75
Basic lighting set for GridLine cabinets withswing doors for cabinet height 900/1000 mm	940501 900/1000
Drawer for swing-door cabinets,Width 20G Drawer front height 200 mm	940640 200
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F
Inclined shelf for cabinet / compartment width in G 20	940560 20
Non-slip mats set for drawers,5 pieces Dimension in G 16X16	951885 16X16
Drawer for swing-door cabinets,Width 20G Drawer front height 125 mm	940640 125
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Ribbed rubber mat for drawers Dimension in G 16X16	951910 16X16
Drawer for swing-door cabinets,Width 20G Drawer front height 100 mm	940640 100
Drawer for swing-door cabinets,Width 20G Drawer front height 300 mm	940640 300
Storage shelf slotted for cabinet / compartment width in G 20	940552 20
Storage shelf for cabinet / compartment width in G 20	940550 20