

Garant
Machine tap for through holes and blind holes, uncoated, Type: 2.3/8-12

Order data

Order number	130050 2.3/8-12
GTIN	4062406052324
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS

Threads per inch: 12

Thread \varnothing : 60.325 mm

Overall length L: 160 mm

Shank \varnothing D_s: 50 mm

Shank square \square : 39 mm

Tapping hole \varnothing : 58.3 mm

Technical description

Tapping hole \varnothing	58.3 mm
Number of clamping slots	6
Number of cutting edges Z	6
Shank \varnothing D _s	50 mm
Thread depth	90.49 mm
Threads per inch	12
Thread \varnothing	60.325 mm
Overall length L	160 mm

Thread pitch	2.11 mm
Shank square <input type="checkbox"/>	39 mm
Tool material	HSS
Thread type	UN
Thread size	2.3/8-12 UN
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for blind holes and through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap