

**Garant**
**Machine tap for through holes and blind holes, uncoated, Type: 3.3/4-10**

**Order data**

Order number	130050 3.3/4-10
GTIN	4062406052935
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS

Tool material: HSS

Threads per inch: 10

Thread  $\varnothing$ : 95.25 mm

Overall length L: 180 mm

Shank  $\varnothing$  D<sub>s</sub>: 56 mm

Shank square  $\square$ : 44 mm

Tapping hole  $\varnothing$ : 93 mm

**Technical description**

Overall length L	180 mm
Number of clamping slots	10
Shank $\varnothing$ D <sub>s</sub>	56 mm
Tool material	HSS
Threads per inch	10
Tapping hole $\varnothing$	93 mm
Thread depth	142.88 mm
Shank square $\square$	44 mm

Number of cutting edges Z	10
Thread Ø	95.25 mm
Thread pitch	2.54 mm
Thread type	UNS
Thread size	3.3/4-10 UNS
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for blind holes and through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap